

Option: stainless steel fork shoes

Nr.	Item code	Description	Special instructions	Quantity
D100	HOP-MP-U-HI-END-RAL3000	Mounting part High End bottom housing universal RAL3000		1,0
D103	IN-MT-256X-WLAN	Indicator Mettler IND 256X terminal, WLAN		1,0
D103	SA-IN-RAVAS-2560X-W	Subassembly, indicator RAVAS 2560X-w, RAL3000		1,0
D117	HOP-LOCK-PRO	Lock Pro		1,0
D118	SAP-HOP-HI-END-TUBE-60MM-STST	Subassembly, set rotating support High End housing stst	Option: rotating indicator	1,0
D119	MP-BASE-ROTATING	Rotating base indicator		1,0
D120	SAP-MP-SUP-256X-STST	Subassembly, Mounting support 256X inox (incl bolts)		1,0
D123	HOP-CP-HI-END-BH-RAL3000	Coverplate High end Housing RAL3000		1,0
D128	SAP-HOP-MC-HI-END-RAL9005	Subassembly, Middle cover High End RAL9005 (incl. bolts)		1,0
D129	SAP-MP-JUNC-HI-END-STST	Subassembly, Mounting plate junction box (incl bolts)		1,0
D133	CA-6-1,25M-MT	Cable 6 x 1,25 Mettler 226X - per piece		1,0
D153	SAO-PTP-R-BRAKE-FO	Subassembly, PT-R Footbrake, for painted Ningbo Ruyi chassis		1,0
D291	SAO-HO-ALU-JUNC-EXI	Subassembly, prepared housing for Junction box EXi		1,0