ProLine 2100L EXi



Nr.	Item code	Description	Special instructions	Quantity
	HOP-KEY-EXI	Key housing EXi	openia instruction	1,0
D3	SA-LC-1000-M-350	Subassembly, load cell 1000 M 350 Ohm, humidity protected		4,0
D4	MP-BOLT-M12-40-CYL-STST	Bolt M12 x 40 socket head stainless steel DIN 912		8,0
D5	MP-BOLT-M12-60-CS-STST	Bolt M12 x 60 countersunk stainless steel din7991, A2	Needed for stainless steel ssytems or systems with stainless steel fork shoes	2,0
D7	MP-NUT-M12-LOCKNUT-STST	Nut M12 lock nut stainless steel din985 A2	Needed for stainless steel ssytems or systems with stainless steel fork shoes	2,0
D8	BA-EXI	Battery pack EXi		1,0
D15	SAO-CH-EXI	Subassembly, charger EXi		1,0
D17	FR-21-TOUCH-PANEL	Front panel 2100 - touch panel		1,0
D18	IN-21-NU-EXI-R76-P7.8	Indicator 2100 NU EXi R76, P7.8 version	Option: Legal for trade	1,0
D75	PT-A-RAL3000	Pallet truck Almeborg 1150x550, RAL 3000		1,0
D77	PTP-A-HANDLE	PT-A Handle complete Almeborg chassis, standard version		1,0
D78	PTP-A-WH-ST-AS-180	PT-A Almeborg wheel steering anti-static Ø180 mm, bearing		1,0
D80	PTP-A-REP	Repair kit for painted/semi stainless hand pallet truck		1,0
_				

Product changes reserved

1/3

Nr. Item code	Description	Special instructions	Quantity
D81 FS-A-STST	Fork shoes Almeborg stainless steel	Option: stainless steel fork shoes for painted systems	1,0
D91 EB-4-LC-21-41	Junction board 4xLC		1,0
D92 SAO-EP-LEVELSWITCH-EXI-C3041	Subassembly, Levelswitch EXi with C3041 chip	Option: legal for trade	1,0
D95 MP-RING-M12	Ring M12, din125A		2,0
D98 HO-HI-END-BH-RAL3000	Bottom housing, Hi-end palletwagen, RAL3000		1,0
D100 HOP-MP-U-HI-END-RAL3000	Mounting part High End bottom housing universal RAL3000		1,0
D116 SAP-MP-LC-FLEXIBLE-V5-STST	Subassembly, Load cell flexbolt, stainless steel with M8 nut	For stainless steel systems and systems with stainless steel fork shoes.	2,0
D117 HOP-LOCK-PRO	Lock Pro		1,0
D118 SAP-HOP-HI-END-TUBE-60MM-STST	Subassembly, set rotating support High End housing stst	Option: rotating indicator	1,0
D119 SAP-MP-BASE-ROTATING	Subassembly, set rotating base indicator (incl bolts)	Option: rotating indicator	1,0
D123 HOP-CP-HI-END-BH-RAL3000	Coverplate High end Housing RAL3000		1,0
D134 SA-HO-JUNC-EXI	Subassembly, Junction box for EX systems	Includes calibration board EB-4-LC-21-41	1,0
D152 MP-WF-BUSH-LC	Bush load cell holes RWV-N		8,0
D153 PTP-A-BRAKE-FO-STST	PT-A Footbrake stainless steel (Almeborg)		1,0
D215 HOP-HI-END-TH-BOTTOM-STST	Bottom plate High End top housing stainless steel		1,0
D231 EP-PUSH-EXI	Push button 2100 EXi		1,0

Product changes reserved 2/3

Print date: 15-2-2023

Nr. Item code	Description	Special instructions (Quantity
D232 INP-MEM-PT	Membrane push button engraved 2100 EXi ")PT"		1,0
D232 INP-MEM-O/T	Membrane push button engraved 2100 EXi ")O/T("		1,0
D232 INP-MEM-E	Membrane push button engraved 2100 EXi "E"		1,0
D233 INP-MEM-O/I	Membrane push button engraved 2100 EXi " O/I "		1,0
D234 MP-NUT-M5-16-NEOPRI	EEN Nut M5 x 16 Neopreen		18,0
D235 HOP-PACK-TH	Enclosure indicator housing		1,0
D241 HO-HI-END-TH-STST-PB-	EXI Top housing stainless steel, Pushbuttons EXi		1,0

Product changes reserved 3/3